

FORMALDEHYDE GAS DETECTOR

Gas Detection For Life

Model FP-30



Features

- · Simple operation
- Specific to Formaldehyde
- · Built-in sample draw pump
- Easy to read LCD display
- · Self-diagnosis
- Uses photoelectric photometry technology
- · Direct digital readout
- · Colorimetric detection tablet method
- · No false readings from interfering gases
- · Operates on 4 AA alkalines
- · Stores 99 readings
- · No warm up time

Applications

- · Furniture and woodworking
- · Coating and varnishing
- · Engineered wood products
- Medical / veterinary
- Painting & corrosion resistant finishes
- · Carpet manufacture & storage
- Adhesives
- Heat treatment operations
- · RV/Trailer/mobil home inspecting

This highly sensitive portable gas detector use photoelectric photometry method with colorimetric detection tab. The sample drawing rate is controlled by a microprocessor. The FP-30 and has a direct readout of measurement value on an LCD display. The Model FP-30 can detect the new World Health Organization level of 0.08 ppm average for 30 minutes.

Detection Ranges

30 minute sample 0 - 0.4 ppm (0.005 ppm/digit)

15 minute sample 0 - 1.0 ppm (0.01 ppm/digit)



Model FP-30

Detection gas	Formaldeyde (HCHO) in air		
Detection range	0-0.4 ppm (0.005ppm/digit)	0-1.0 ppm (0.01 ppm/digit)	
Detection time	30 minutes (1,800 sec.)	15 minutes (900 sec.)	
Detection principle	Photoelectric photometry method		
Detection method	Colorimetric tablet method (accumulating measurement)		
Accuracy	± 10% of reading or ± 5% of full scale (which ever is greater)		
Display	Digital LCD		
Sampling method	Sample drawing with built-in pump		
Operating conditions	-10 ~ 40°C (14 ~ 104°F), below 90%RH		
Memory	Detection point: Up to 99 points (automatic recording at the completion of measurement)		
Self-diagnosis	Failure of light source and light receiver, low battery voltage, pump failure, system trouble		
Power Source	AA size Alkaline batteries (quantity 4)		
Continuous Operation	Approximately 12 hours (with no alarm or backlight, with alkaline batteries at 20°C)		
Dimension	Approx 85(W) x 190(H) x 40(D)mm, 3.35(W) x 7.48(H) x 1.57(W),		
Weight	500g, 17.6 oz		
Standard Accessories	Detection TAB (20 pcs/pack) ** Carrying case AA size alkaline batteries Operating manual		
Warranty	One year material and workmanship		

Interference against other gases (typical)			
Test Gas	Concentration	Reading	
Toluene	1.0 vol.%	0 ppm	
Benzene	1.0 vol.%	0 ppm	
Acetoaldehyde	100 ppm	0 ppm	
Carbon monoxide	50 ppm	0 ppm	
Carbon dioxide	1.0 vol.%	0 ppm	
Ammonia	25 ppm	0 ppm	
Acetone	1.0 vol.%	0 ppm	

Field Test Verification Data				
Measurement Place	FP-30	DNPH method*		
Interior	0.020 ppm	0.025 ppm		
Locker	0.030 ppm	0.03 ppm		
Furniture	0.040 ppm	0.05 ppm		

- Dinitrophenylhydrazine detection method Please note: Detection tabs have a 6 month shelf life. They must be stored in a referigerator (37°F-50°F, 3-10°C)

Note: Specifications subject to change without notice.





Toll Free: (800) 754-5165 · Phone: (510) 441-5656 Fax: (510) 441-5650 · www.rkiinstruments.com

Authorized Distributor: